



Assembly Instructions

Use thumbs to press on white/black surfaces

Step 1: fix 19591 to APL

Step 2: if IP 54, fit 19593 inside 19591

Step 3: Click 19592 onto 19591

⌋ Retainer clip for 1.5 mm cladding

⌋ Retainer clip for 2.0 mm cladding

Note: 1.5 mm cladding: ALL clips clicked
2.0 mm cladding: only the black clips clicked

Q&A

Q: How do I order the new louvres?

A: Use LogCad as usual – The new louvres are ready to be shipped. You will need to update the LogCad library; follow the link provided in the news-mail.

Q: Does the old metal louvers still fit the APLs?

A: The welded studs on the APLs become obsolete within 3-6 months from September 2017.

Q: Can I still order APLs compatible with the old metal louvres?

A: Yes, this is still possible if requested explicitly in the order.

Q: Which IP class options are available with the new Louvres?

A: The new louvres offer either IP 33 by default or IP 54 with the addition of an optional filter.

Associated Changes

- For flat plates with louvres we introduce a range of AGLs that follow the same modular sizes as APLs. The new AGLs will effectively replace the OHW naming. The OHW will eventually be removed.

The sizes are (for both APL and AGL):

- 1 to 7 modules in X-axis
- 1 to 3 modules in Y-axis, where
- Y3 can either be fitted with 1, 2, or 3 rows of louvres.